

## IRIS

LED SCIALYTIC DENTAL LIGHT



### WHY IRIS


- for a COMFORTABLE VISION, without shadows
- for an easy and SAFE CLEANING
- antipolimerization mode  
for UNHURRIED TEETH RESTORATIONS
- surgical mode and colour-matching mode,  
for SIGHT EFFICIENCY



### WHY G.COMM



We focus on R&D  
and we apply innovative  
technologies



We are proud to be a manufacturer  
and our whole production chain is  
in Italy



We are close to customers  
and support them with  
qualified technical assistance

**G.Comm**

Via XXV Aprile, 20  
20884 Sulbiate (MB)  
Tel. (+39) 039 60 60 420



[www.gcomm-online.com](http://www.gcomm-online.com)

Discover IRIS  
watch VIDEO



# IRIS



- LED TECHNOLOGY: 8 leds
- SCIALYTIC EFFECT: 80 overlapping rays minimise shadows on the operating field.
- 3 TREATMENT LIGHT PROGRAMS
- ADJUSTABLE COLOUR TEMPERATURE from 4.200 to 6.000K
- ADJUSTABLE LIGHT INTENSITY from 8.000 to 50.000 LUX
- POWER SUPPLY 12/24 AC - 12/24 DC
- 3rd AXIS MOVEMENT
- FRONT COVER
- ALUMINIUM STRUCTURE
- CRI >95
- 2 YEARS WARRANTY\*  
\* on structural components

## RAL colours



## Technical Specifications



### Control keyboard

Colour temperature  
Light Intesity  
Pre-set programs



### ON/OFF Switch

Easy to use, in a comfortable position



### ON/OFF Sensor

Turn the light on/off with a simple gesture: maximum hygiene



### Mirror Kit

It fosters the communication with patients  
Easy hook-on